




















CARTA

SULFÚRICOS - AL AZUFRE


 998 268 034 |  ventas@joelsaimport.com

www.joelsaimport.com 

| Azufre | | Dyeing depth (%o.w.f) | C.I.No. (sulphur) | Dye:50% sodium sulphide | Dyeing temp.°C | Oxidizing method | Fastness Properties | | | | |
|-------------------------|-------------------------------------------------------------------------------------|-----------------------|-------------------|-------------------------|----------------|------------------|---------------------|---------------|--------------|---------|-----|
| | | | | | | | Light (Xenon) | Washing 40 °C | Perspiration | Rubbing | |
| Nombres de Azufre | Muestra de color | | | | | | | | Dry | Wet | |
| Light yellow GC 250% |  | 5.0 | Y 2 | 1:2.5 | 90-95 | C | 3 | 2 | 4 | 3-4 | 3 |
| Light yellow GR 250% |  | 5.0 | Y 2 | 1:2.5 | 90-95 | C | 3 | 2 | 4 | 3-4 | 3 |
| Brill. yellow G 100% |  | 5.0 | Y 9 | 1:1.5 | 90-95 | A.C | 4 | 3-4 | 4 | 4-5 | 3-4 |
| Yellow brown 5G 150% |  | 5.0 | Br* 10 | 1:1.5 | 90-95 | A | 3 | 2-3 | 4 | 3-4 | 2-3 |
| Yellow brown 6G 150% |  | 5.0 | O 1 | 1:1.5 | 90-95 | A | 3 | 3-4 | 4 | 4 | 3 |
| Bordeaux 3B 100% |  | 5.0 | R* 6 | 1:4 | 90-95 | C | 3 | 2-3 | 4 | 3 | 2-3 |
| Red LGF 100% |  | 5.0 | R 14 | 1:1 | 90-95 | A | 4 | 4-5 | 4-5 | 4-5 | 3 |
| Brown GR 100% |  | 4.0 | - | 1:1.5 | 90-95 | C | 3 | 3-4 | 4-5 | 4 | 3 |
| Brown GRN 150% |  | 5.0 | - | 1:1.5 | 90-95 | C | 3-4 | 4 | 4-5 | 3-4 | 3 |
| Brown BR 100% |  | 4.0 | - | 1:1.5 | 90-95 | C | 2-3 | 3-4 | 4-5 | 4-5 | 3 |
| Dark brown GD 150% |  | 5.0 | Br 4 | 1:1.5 | 90-95 | ABC | 4 | 4 | 4 | 4 | 2 |
| Light green 300% |  | 5.0 | G 14 | 1:3 | 80-85 | C | 6-7 | 4-5 | 4-5 | 4-5 | 2-3 |
| Brill. Green GB 100% |  | 5.0 | G 3 | 1:0.75 | 50-60 | AB | 5 | 3-4 | 4 | 4-5 | 3 |

| Azufre | | Dyeing depth (%o.w.f) | C.I.No. (sulphur) | Dye:50% sodium sulphide | Dyeing temp.°C | Oxidizing method | Fastness Properties | | | | |
|-------------------------|-------------------------------------------------------------------------------------|-----------------------|-------------------|-------------------------|----------------|------------------|---------------------|---------------|--------------|---------|-----|
| | | | | | | | Light (Xenon) | Washing 40 °C | Perspiration | Rubbing | |
| Nombres de Azufre | Muestra de color | | | | | | | | Dry | Wet | |
| Olive green 519 200% |  | 5.0 | - | 1:2 | 90-95 | A | 4 | 4 | 3 | 4 | 2-3 |
| Olive green 715 200% |  | 5.0 | - | 1:2 | 90-95 | A | 4 | 4 | 3 | 4 | 2-3 |
| Dark green 511 300% |  | 5.0 | - | 1:2 | 90-95 | C | 5 | 4 | 3 | 3-4 | 2-3 |
| Dark green 611 300% |  | 5.0 | - | 1:2 | 90-95 | C | 5 | 4 | 3 | 3-4 | 2-3 |
| Blue BRN 150% |  | 5.0 | B* 7 | 1:2 | 70-75 | C | 5-6 | 3-4 | 3-4 | 3-4 | 2 |
| Blue BN 150% |  | 5.0 | B 7 | 1:2 | 70-75 | C | 5-6 | 3-4 | 3 | 3-4 | 2 |
| Blue 2BN 150% |  | 5.0 | B 7 | 1:2 | 70-75 | C | 5-6 | 3-4 | 3 | 3-4 | 2 |
| Dark blue 3R 100% |  | 5.0 | B 5 | 1:1.5 | 80-85 | BC | 5 | 4 | 3-4 | 4 | 2 |
| Dark blue 3R 130% |  | 5.0 | B 5 | 1:1.5 | 80-85 | BC | 5 | 4 | 3-4 | 4 | 2 |
| Blue BBF 100% |  | 5.0 | B 13 | 1:2 | 60-70 | B | 5-6 | 4 | 2-3 | 4-5 | 2-3 |
| Sky blue CV 100% |  | 5.0 | B 15 | 1:1.5 | 90-95 | B | 6-7 | 3-4 | 3 | 4 | 2 |
| Sky blue CV 120% |  | 5.0 | B 15 | 1:1.5 | 90-95 | B | 6-7 | 3-4 | 3 | 4 | 2 |
| Black BR 200% |  | 8.0 | Bk* 1 | 1:3 | 90-95 | A | 6 | 3-4 | 4 | 3-4 | 2 |

| Azufre | | Dyeing depth (%o.w.f) | C.I.No. (sulphur) | Dye:50% sodium sulphide | Dyeing temp.°C | Oxidizing method | Fastness Properties | | | | |
|-------------------|-----------------------------------------------------------------------------------|-----------------------|-------------------|-------------------------|----------------|------------------|---------------------|---------------|--------------|---------|-----|
| | | | | | | | Light (Xenon) | Washing 40 °C | Perspiration | Rubbing | |
| Nombres de Azufre | Muestra de color | | | | | | | | | Dry | Wet |
| Black BN 200% |  | 8.0 | Bk 1 | 1:3 | 56-70 | A | 6 | 3-4 | 4 | 2-3 | 1-2 |

| Azufre Líquido | | Dyeing depth (%o.w.f) | C.I.No. (sulphur) | Dyeing tempo. oc | Oxidizing method | Fastness Properties | | |
|-------------------|-------------------------------------------------------------------------------------|-----------------------|-------------------|------------------|------------------|---------------------|---------------|---------|
| | | | | | | Light (Xenon) | Washing 40 °C | Rubbing |
| Nombres de Azufre | Muestra de color | | | | | | | |
| Light yellow G |  | 15 | Y 9 | 60-70 | AC | 3-4 | 3-4 | 2-3 |
| Light yellow GC |  | 15 | Y 2 | 60-70 | C | 3-4 | 3-4 | 2-3 |
| Bright green BF |  | 15 | G 14 | 60-70 | C | 3-4 | 3-4 | 2-3 |
| Brill. green GB |  | 15 | G 3 | 60-70 | AB | 3-4 | 3-4 | 2-3 |
| Olive green D |  | 15 | Mix | 60-70 | A | 3-4 | 3-4 | 2-3 |
| Green blue CV |  | 15 | B 15 | 40-50 | B | 3-4 | 3-4 | 2-3 |
| Blue BN |  | 15 | B 7 | 40-50 | C | 3-4 | 3-4 | 2-3 |
| Red LGF |  | 15 | R 14 | 60-70 | A | 3-4 | 3-4 | 2-3 |
| Navy blue SB |  | 15 | B 5 | 60-70 | BC | 3-4 | 3-4 | 2-3 |
| Black BR |  | 20 | Bk 1 | 90-95 | A | 3-4 | 3-4 | 2-3 |

Nuestras cartas cuentan con colores referenciales.