








CARTA

BÁSICOS

 998 268 034 |  ventas@joelsaimport.com





www.joelsaimport.com 

BÁSICOS		Dyeing depth (%o.w.f)	C.I.No. (Basic)	K Value	F Value	Fastness Properties				
						Light (Xenon)	Washing 60 °C	Perspiration	Rubbing	
									Dry	Wet
Nombres de Básicos	Muestra de color									
Auramine O 100%		0.4	Y* 2	/	/	1	1	3-4	3-4	4-5
Yellow 8GL 250%		0.8	Y 13	3.5	0.75	3-4	4-5	4-5	4-5	4-5
Yellow 7GLL 200%		0.8	Y 21	2.5	0.29	4-5	4-5	4-5	5	4-5
Brill. Yellow 7GL 500%		0.8	Y 24	1.5	0.52	3	4-5	4-5	5	5
Golden Yellow X-GL 250%		0.8	Y* 29	3	0.61	6-7	4-5	4-5	4-5	4-5
Yellow X-GRL 200%		0.8	Y* 28	2	0.6	6-7	4-5	4-5	4-5	4-5
Flavine 10GFF 300%		0.8	Y* 40	3.5	0.5	3	4-5	4-5	5	5
Yellow M-RL		0.6	Y 49	0.5	0.52	5	3-4	4-5	4-5	4-5
Yellow 5GL 400%		0.5	Y* 51	3	1	6	4-5	4-5	4-5	4-5
Yellow 4GL 100%		0.6	Y 87	3	0.74	7	4-5	4-5	4-5	4-5
Chrysoidine G 100%		0.4	O* 2	3	1	2	2-3	4-5	4	3-4
Orange G 400%		0.4	O 21	1.5	0.4	5	4-5	5	5	5
Rhodamine 6GDN		0.4	R 1	/	/	2	3	4-5	/	/

BÁSICOS		Dyeing depth (%o.w.f)	C.I.No. (Basic)	K Value	F Value	Fastness Properties			
						Light (Xenon)	Washing 60 °C	Perspiration	Rubbing
Nombres de Básicos	Muestra de color							Dry	
Rhodamine 6GD		0.4	R 1:1	/	/	2	3	3-4	/
Red P 60%		0.6	R 12	/	/	1-2	3-4	/	/
Pink FG 250%		0.6	R 13	4	0.46	3-4	4	4-5	4-5
Red X-5GN 250%		0.4	R* 14	3	0.5	3-4	4-5	4-5	4-5
Brill. Red B 250%		0.8	R* 15	3.5	0.36	4-5		5	5
Red GTL 200%		0.6	R 18	2.5	0.72	5-6	4-5	4-5	4-5
Red GTLN 200%		0.4	R 18:1	3	0.39	7	4-5	5	4-5
Red 2GL 250%		0.6	R 29	1.5	0.52	7	4	4	4-5
Red GRL 250%		0.6	R* 46	2.5	0.43	2-7	6-7	4-5	5
Brill. Red BN 250%		0.8	R* 49	/	0.39	3-4	4-5	5	5
Red M-RL 200%		0.6	R 51	3	0.4	6	5	5	5
Methyl V2B 100%		0.4	V* 1	/	/	1-2	3-4	4-5	/
Methyl V5BN 100%		0.4	V* 3	/	/	1	1-2	1-2	4

BÁSICOS		Dyeing depth (%o.w.f)	C.I.No. (Basic)	K Value	F Value	Fastness Properties				
						Light (Xenon)	Washing 60 °C	Perspiration	Rubbing	
									Dry	Wet
Nombres de Básicos	Muestra de color									
Red 6B 200%		1	V 7	3	0.19	3-4	4	4	4-5	
Rhodamine B 500%		0.4	V 10	/	/	2	3-4	3-4	4	
Rhodamine BL-ED		0.4	V 11	/	/	1	1	1	/	
V11:1		0.4	V 11:1	/	/	2	/	/	/	
Magenta 100%		0.4	V 14	/	/	1	2	3-4	4-5	
Violet 3R 300%		0.6	V* 16	1.5	0.5	3-4	4-5	4	4-5	
Brill. Violet 5BLH 200%		0.5	B 62	3	0.49	4-5	4-5	4-5	5	
Violet 3BL 250%		0.5	B 53	1.5	0.31	5	3-4	4	4-5	
Turq. Blue X-GB 250%		0.4	B* 3	3.5	0.75	4-5	4-5	4-5	4-5	
Victoria blue BO 100%		0.4	B* 7	/	/	2	4	4	3	
Methyleneç blue 2B 100%		0.4	B 9	/	/	2	3	4	4	
Victoria blue R		0.4	B 11	/	/	2	4-5	4	3	
Victoria blue B		0.4	B* 26	/	/	2	4	4	3	

BÁSICOS		Dyeing depth (%o.w.f)	C.I.No. (Basic)	K Value	F Value	Fastness Properties				
						Light (Xenon)	Washing 60 °C	Perspiration	Rubbing	
Nombres de Básicos	Muestra de color								Dry	Wet
Blue X-GRL 300%		0.4	B* 41	3	0.4	6	4	4	4-5	4-5
Blue X-GRRL 250%		0.4	B* 41	3	0.4	6	4	4	4-5	4-5
Brill. Blue RL 100%		0.2	B 54	1.5	0.67	5-6	4-5	4	4-5	4-5
Blue FRL 100%		0.2	B 162	3	0.14	4-5	4-5	4-5	5	5
Navy blue 2RN 200%		1-5	-	3	0.5	3-4	4-5	4	4-5	4
Navy blue X-BRL 300%		1.5	-	3	0.58	5-6	4-5	4-5	4	4
Navy blue X-BL 250%		0.4	B* 159	3	0.43	6-7	4-5	4-5	4-5	4-5
Dark blue RB 300%		1.5	-	3	0.47	4-5	4	4-5	4-5	3-4
Malachite Green 100%		0.4	G* 4	4.5	/	4-5	/	4	4	4
Bismark brown G 100%		0.4	Br 1	/	/	2	4	4	3-4	3-4
Bismark brown R 100%		0.4	Br 4	/	/	1	1	4	/	/
Black X-O 300%		1.5	-	3	1	4-5	4-5	4-5	4	/
Black X-FBL 300%		2	-	3	0.35	6	4	4-5	4-5	4

BÁSICOS LÍQUIDOS		Dyeing depth (%o.w.f)	C.I.No. (Basic)	K Value	F Value	Fastness Properties				
						Light (Xenon)	Washing 60 °C	Perspiration	Rubbing	
Nombres de Básicos	Muestra de color								Dry	Wet
Brown 25LN		0.6	Br 19	/	/	/	/	/	/	/
Brown M-2R		0.6	Br 23	/	/	1	/	/	/	/
Orange 63		0.8	O 63	/	/	/	/	/	/	/
Yellow 96		0.8	Y 96	/	/	/	/	/	/	/

Nuestras cartas cuentan con colores referenciales.